




Notes:
Rated current:3.0A
Withstand Voltage:500V AC/DC
Contact Resistance:20mΩ Max
Insulation Resistance:1000MΩ Min
Operating Temperature:-40℃ TO +105℃
Contact Material:Brass
Plating:Gold flash
Insulator Material: PA6T UL94V-0 BK

G	NO.	DATE	DESCRIPTION	APPROVAL	DRAWING:	GENERAL TOLERANCE .X: ±0.30 .X*: ±2" .XX: ±0.20 .XX*: ±1" .XXX: ±0.10 .XXX*: ±0.5"		东莞市文章济美电子有限公司	
	1	2024-05-28	初次发行	Jack	MAO ZI HAO				
	2				CHECKED:	UNIT: MM PROJECTION		DESCRIPTION: 2.54x2.5 1xNP PA6.0 PC3.0 L11.6	
	3				YAO HUI SONG				
	4				APPROVAL:	SCALE: N/A SHEET: 1/1		PART NO: REC:1.0 SERIES : ROHS	
H	5				HAN XIAO QIU				