






3D VIEW



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)




- NOTES:
1:MATERIAL:
1-1:STAINLESS STEEL THICKNE=0.08±0.03mm
2:FINISH:
2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.
2-2:DIMENSIONS OF PCB PAD STENCIL
ARE FOR REFERENCE ONLY,
CUSTOMER CAN MODIFY IT BY THEIR OWN.
3:PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.5A/MAX
3-2:VOLTAGE RATING:5.0V/AC/DC/MAX
3-3:CONTACT RESISTANCE:50mΩ/MAX
3-5:OPERATING TEMPERATURE:-40°C~85°C
3-6:NORMAL FORCE OF PRESS@0.50:18gf±8gf.
3-7:DURABILITY:10,000 CYCLES.
4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)
5:PACKING SPECIFICATION:REEL&TARE
6:DIMENSIONS MARKED ■ ,CPK>1.33
7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;
8:COMPLIANT TO RoHS&LEAD FREE




深圳市华宇创精密电子有限公司


TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: L2. 97*W1.34*H4.10mm 立式充电弹片	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT29713441TAB	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2609031501	
			SHEET NO. 1 OF 1	



耳机插入力曲线图(仅供参考)




耳机插入示意图(仅供参考)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: L2. 97*W1.34*H4.10mm立式充电弹片	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HWCW-TXT29713441TAB	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2609031501	
			SHEET NO. 1 OF 1	

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X* $\pm 2^{\circ}$ X.X* $\pm 0.5^{\circ}$		DRAWN BY : 陈一鸣 2014-02-23	
 UNIT: mm [inch]		CHECKED BY: 马跃 2014-02-23	
		APPROVED BY: 邱敏 2014-02-23	
SCALE: 1:1 SIZE: A4		PART NAME: 包装图 PART NO. MOLD NO. DRAW NO: SHEET NO. 1 of 1	