Dersonic®
德信立業 創新開拓

承认书

APPROVAL SHEET

客户 CUSTOMER	立創商城
客户料号 CUSTOMER P/N	
规格描述 DESCRIPTION	400V/0.22UF/J/卧式/L35/9*19/ZNRC/MPT
产品编码 PART NUMBER	CFT2G224J0D01909D200
日期 DATE	2026-06-01

德尔创承认栏 APPROVED BY DERSONIC			客户承认栏 APPROVED BY CUSTOMER	
批　准 APPROVED BY	审核 CHECK BY	制订 FORMULATE BY	批　准 APPROVED BY	审核 CHECK BY
彭少雄	吴成爱	胡明康		

东莞市德尔创电子有限公司 样品承认章

东莞市德尔创电子有限公司
DONGGUAN DERSONIC ELECTRONIC CO., LTD.
广东省东莞市寮步镇松湖智谷产业园F2栋15楼
15/F, Blk F2, Songshan Lake Intelligent Valley Industrial Park,Liaobu Town, Dongguan City, PRC
TEL: +86-769-8155 5686　　FAX: +86-769-8155 5989
E-mail: sales@dersonic.com　　quality@dersonic,com
Website: http://www.dersonic.com

TECHNICAL PARAMETERS

ELECTRICAL CHARACTERISTICS：

1	Rated capacitance (C_R)	0.22μF
2	Capacitance tolerance	±5%
3	Rated voltage(VR)	400VDC

TEST PARAMETERS：

4	Voltage proof between terminals	Apply 1.5 times of U_R for 60 +/-5sec. or 1.75 times of U_R for 2 sec.
5	Insulation resistance(IR* C_R)	CR≤0.33μF >30000MΩ CR>0.33μF ≥10000MΩ/uF (20℃ 1Min)
6	Dissipation factor(DF)	≤0.001（20℃ 1KHz）

WORK ENVIRONMENT：

7	Climatic category	40/85/21
8	Operating temperature range	-40°C to +85°C
9	Standard	IEC60384-16


CONSTRUCTION：

10	Dielectric	Metallized polypropylene
11	Metal spray	Special Solder
12	Filler	Epoxy resin
13	Outer envelope	Mylar Tape
14	Lead wire	Lead wire diameter 0.8mm

Other

Product Dimensions in mm

P/N	Dimension(mm)					CUSTOMER P/N
	W (Max)	φD (Max)	L (Min)	φd ±0.05	/	
CFT2G224J0DO1909D200	19.0	9.0	35.0	0.8	/	



FNAME REVDATE USER