








REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
X1	/	NEW	2026.02.27	Qiang	GONG	LEO



RECOMMENDED REFLOW TEMPERATURE PROFILE
USIN LEAD-FREE SOLDER PASTE



RECOMMENDED METAL DIMENSIONS (THICKNESS: 0.08 mm)

NOTES:


- 1.0 VOLTAGE: 50V AC/DC
- 2.0 CURRENT: 0.3A/SIGNAL CONTACT, 5A/POWER CONTACT
- 3.0 OPERATION TEMPERATURE: -40° C TO 85° C
- 4.0 CONTACT RESISTANCE(INITAIL): 70mΩ /SIGNAL CONTACT, 15mΩ /POWER CONTACT
(AFTER TEST): 100mΩ /SIGNAL CONTACT, 20mΩ /POWER CONTACT
- 5.0 INSULATION RESISTANCE: 50MΩ MIN INITIAL
- 6.0 DIELECTIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE
- 7.0 MATING:40N Max
UNMATING FORCE:(INITAIL)5N Min;(AFTER TEST)4N Min
- 8.0 DURABILITY:30 CYCLES
- 9.0 IR REFLOW CYCLE: 2 CYCLES MAX.

3	POWER CONTACT	COPPER ALLOY, Au4u" Min ON CONTACT AREA, Au2u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER	6	REEL	PLASTIC
2	SIGNAL CONTACT	COPPER ALLOY, Au4u" Min ON CONTACT AREA, Au2u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER	5	COVER TAPE	PLLYESTER
1	HOUSING	LCP , BLACK, UL 94 V-0	4	EMBOSSED CARRIER TAPE	PS
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS
GENERAL	TOLERANCE	UNITS:mm SCALE 1 : 1	TITLE: BTB CONN, Plug, MH0. 60, P0. 35mm (16Pin)		
X. ± 0.30	X.* ± 5°	APPROVED	DRAWING NO. : C-BB0030P-5		
.X ± 0.20	.X* ± 3°	CHECKED	PART NO. : BB0030P16A		
.XX ± 0.15	.XX* ± 2°	DESIGNED			


Rohs 2.0
Compliant



HF



DIRECTION OF UNREELING



STYLE AND DIMENSION OF REEL
PER REEL 15000 CONNECTORS

NO.				NO.			
PART NAME				PART NAME			
DESCRIPTION, REMARKS				DESCRIPTION, REMARKS			
GENERAL	TOLERANCE	UNITS:mm	SCALE 1 : 1	TITLE: BTB CONN, Plug, MH0. 60, P0. 35mm (16Pin)			
X. ± 0.30	X.* ± 5°	APPROVED	LEO	DRAWING NO. : C-BB0030P-5			X1
.X ± 0.20	.X* ± 3°	CHECKED	GONG	PART NO. : BB0030P16A			2/2
.XX ± 0.15	.XX* ± 2°	DESIGNED	Qiang				

CPT 元精技术