








客户图 32905-707-3



Cool cray 5C 潘通(PANTONE) 塑胶颜色色号 封年/月,模穴號

• 外殼產品需做如下標示(位置不限)
<1>件號: 32905-707
<2>材質: >PC V0<
<3>生產年/月(必須與當時生產年/月一致)

NO.	ECN NO.	DESCRIPTION	DATE
		防止縮水, 塑胶加强筋, 骨位结构减胶变更。	2020.12.15
		增加4个锁螺丝定位柱。	2021.2.28

Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

Plastic: PC V0 cool cray 5c (塑胶: PC V0 冷灰色 5c)

2: Plating(电镀):

Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: Gold flash (弹簧: 镀金1u')

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;10A (额定电压&电流: 直流12V,10A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):



Force: 140g±20% at working height. (140g±20% 在工作高度)。

Durability: 100.000 cycles(min) (寿命: 100000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃



深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2026.7.27	VER.	0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZP0401-60150-04042-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			