


## 客户图

| NO. | ECN NO. | DESCRIPTION | DATE       |
|-----|---------|-------------|------------|
| 1   |         | 首次发行        | 2014.05.31 |



## Note:

## 1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

## 2: Plating(电镀):

Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: NO flash (弹簧: 不电镀)

## 3: Electrical(电气特性):

Rated Current &amp; Voltage: DC 12V;1A (额定电压&amp;电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

## 4: Mechanical(机械性能):

Force: 40g±20% at working height. (40g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

## 5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

|        |            |            |     |
|--------|------------|------------|-----|
| SCALE: | N/A        | UNIT       | mm  |
| SHEET: | 1 of 1     | PROJECTION |     |
| DATE:  | 2020.01.10 | VER.       | A.0 |

## THE UNMARKED TOLERANCE ARE AS BELOW:

| LENGTH |         | ANGLE |        |
|--------|---------|-------|--------|
| X.XX   | ±0.05mm | X.XX  | ±0.50° |
| X.X    | ±0.10mm | X.X   | ±1.00° |
| X.     | ±0.20mm | X.    | ±2.00° |

|              |     |          |                  |
|--------------|-----|----------|------------------|
| DESIGNED BY: | lyg | DWG. NO. | YZP0292-14055-01 |
| CHECKED BY:  |     | TITLE:   | Pogo Pin         |
| APPROVED BY: |     |          |                  |