





NO.	ECN NO.	DESCRIPTION	DATE

Note:

- 1: Material(材料) :
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀) :
Barrel: 50~80u' Ni(针管: 镀镍50~80u'.)
Plunger: 50~80u' Ni(针管: 镀镍50~80u'.
Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V;10A (额定电压&电流: 直流12V,10A)
Contact Resistance: 500 mohm Max. at working height.
接触电阻: 最大500毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能) :
Force: 180g±20% at working height. (180g±20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: ?20℃~ ?70℃
- 6: 针头拔出力: 不低于1Kg.



工作状态

深圳市鑫探技术有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2016.09.12	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZP0007-44075-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			