


	8	9	10	11	12
NO.	ECN NO.	DESCRIPTION			DATE

客户图



Note:

1: Material(材料) :

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 1u' Au over 50~80u' Ni(针管: 镀金1u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80'u Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;10A (额定电压&电流: 直流12V,10A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻：最大**50毫欧**（在工作高度状态下）

4: Mechanical(机械性能):

Force: 60g±20% at working height. (60g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280c

Operational Temperature: ?40c~ ?85c

深圳市鑫探技术有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZP0101-25093-01
SHEET:	1 of 1	PROJECTION						LENGTH ANGLE			
DATE:	2018.06.01	VER.	A.1	X.XX ±0.05mm X.X ±0.10mm X. ±0.20mm	X.XX ±0.50° X.X ±1.00° X. ±2.00°	APPROVED BY:					