



客户图

| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
| 1   |         |             |      |



外观面



技术要求:

- 材料 黄铜C3604;
- 不允许有批锋, 毛刺; 切断点最大不超过0.03mm。
- 镀金3u', 镍底50-80u';

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



|        |           |            |     |
|--------|-----------|------------|-----|
| SCALE: | N/A       | UNIT       | mm  |
| SHEET: | 1 of 1    | PROJECTION |     |
| DATE:  | 2025.9.11 | VER.       | A.0 |

| THE UNMARKED TOLERANCE ARE AS BELOW : |         |       |        |
|---------------------------------------|---------|-------|--------|
| LENGTH                                |         | ANGLE |        |
| X.XX                                  | ±0.05mm | X.XX  | ±0.50° |
| X.X                                   | ±0.10mm | X.X   | ±1.00° |
| X.                                    | ±0.20mm | X.    | ±2.00° |

|              |  |          |                  |
|--------------|--|----------|------------------|
| DESIGNED BY: |  | DWG. NO. | YZT1189-25045-G3 |
| CHECKED BY:  |  | TITLE:   | 车件               |
| APPROVED BY: |  |          |                  |