







技术指标:

1. 零件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC
(使用AWG#28~#32, O.D 0.6mm MAX).
7. 耐电压: AC 200V/1分钟.

材质:

1.LCP 本色



Part No	CKT	A	B	C	D
XY-0.8-2A41-G	2	0.80	1.80	2.30	4.30
XY-0.8-3A41-G	3	1.60	2.60	3.10	5.10
XY-0.8-4A41-G	4	2.40	3.40	3.90	5.90
XY-0.8-5A41-G	5	3.20	4.20	4.70	6.70
XY-0.8-6A41-G	6	4.00	5.00	5.50	7.50
XY-0.8-7A41-G	7	4.80	5.80	6.30	8.30
XY-0.8-8A41-G	8	5.60	6.60	7.10	9.10
XY-0.8-9A41-G	9	6.40	7.40	7.90	9.90
XY-0.8-10A41-G	10	7.20	8.20	8.70	10.70
XY-0.8-11A41-G	11	8.00	9.00	9.50	11.50
XY-0.8-12A41-G	12	8.80	9.80	10.30	12.30
XY-0.8-13A41-G	13	9.60	10.60	11.10	13.10
XY-0.8-14A41-G	14	10.40	11.40	11.90	13.90
XY-0.8-15A41-G	15	11.20	12.20	12.70	14.70
XY-0.8-16A41-G	16	12.00	13.00	13.50	15.50
XY-0.8-17A41-G	17	12.80	13.80	14.30	16.30
XY-0.8-18A41-G	18	13.60	14.60	15.10	17.10
XY-0.8-19A41-G	19	14.40	15.40	15.90	17.90
XY-0.8-20A41-G	20	15.20	16.20	16.70	18.70
XY-0.8-21A41-G	21	16.00	17.00	17.50	19.50
XY-0.8-22A41-G	22	16.80	17.80	18.30	20.30
XY-0.8-23A41-G	23	17.60	18.60	19.10	21.10
XY-0.8-24A41-G	24	18.40	19.40	19.90	21.90
XY-0.8-25A41-G	25	19.20	20.20	20.70	22.70

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 0.8 Pitch C 型 WTB 4 针 连接器			
.X $\pm$ 0.5	X.* $\pm$ 1°	APR.	Alex	DWG NO. XY-0.8-NA41-G	
.XX $\pm$ 0.2	.X° $\pm$	CHK.	Jack	PROJ.  CUSTOMER DRAWING	
.XXX $\pm$ 0.1	.XX° $\pm$	DRA.	Can	SIZE A4	SCALE 1:1
		SHEET 1/1		REV.	A