











RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



NOTES:

1. MATERIAL:
   - 1.1 HOUSING:THERMOPLASTIC FLAMMABILITY RATING UL94-O
   - 1.2 CONTACT:COPPERY ALLOY T=0.20MM
   - 1.3 SHELL: COPPERY ALLOY T=0.25MM
2. FINISH:
   - 2.1 CONTACT:
     - 0.5U"MIN,PLATED ON CONTACT AREA
     - G/F PLATING ON SOLDER TAIL AREA
     - 40~50U" NICKEL UNDERPLATING OVERALL
   - 2.2 SHELL:
     - 50~60U" MATTER TIN PLAING ALL
     - 40~50U" NICKEL UNDERPLATING OVERALL
3. SPECIFICATION:
   - 3.3 CURRENT RATING:0.5A(2.3.4CONTACT)/1.8A (1.5CONTACT)MAX.
   - 3.2 VOLTAGE:30 VAC
   - 3.3 TEMPERATURE RANGE:-20°C~85°C
   - 3.4 CONTACT RESISTANCE:30 MILLIONHM MAX.
   - 3.5 DIELECTRIC WITHSTANDING VOLTAGE;250VAC R.M.S
   - 3.6 INSULATION RESISTNACE:100 MEGOHMS MIN

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD
CHECKED:	DATE:	TITLE: Micro usb 5P B型 SMT 全贴 无柱 卷边
DRAWN: YKX	DATE: 2024-07-14	PART.NO. U-MICRM05P-BF10
		UNIT mm SCALE free
		FILE NO. Ckmtw-MICRO-0072 REV. A HK01