


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW		


RoHS Compliant








SECTION A—A














RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

备注:
1.材质:
1.1胶壳:LCP+30%G.F UL94V-0 黑色
1.2端子:黄铜C2680 :镀底40U" MIN
镀金区域镀金(AU 0.8u")焊接区域镀金G/F
1.3外壳:SUS304.T=0.30mm:表面镀镍40-60U"MIN
1.4中夹片:SUS201:
2.主要特性:
2.1额定电流:3A
2.2接触阻抗:40mΩ MAX(初始值)
50mΩ MAX(测试后)
2.3绝缘阻抗:100MΩ MIN
2.4耐压测试:100V AC R M S
2.5座体插入力:5-20N 座体插入力:5-20N(耐久后)
座体拔出力:8-20N 座体拔出力:6-20N(耐久后)
2.6耐久:10000次
2.7耐高温:SMT回流焊(峰值260°±5°),温度不能有起泡,
跟胶等不良,变色,温度变形不在范围以内.
2.8产品镀层厚度测试,结晶面积达到95%以上
2.9盐雾测试:48H MIN
3.0工作温度:-25℃~+80℃

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司 Guangdong Chuangyue Technology Co.,Ltd
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE-C 6PIN 中夹片四脚插板上型
.XX ±0.20	.XX° ± 0.5°	FINISH	TYPE-C-6P-L6.8SMT-30113 PART NO.:
.XXX ± 0.10		CHKD:	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., Ltd		Q'TY	DR: SCALE 1/1 SHEET 1/1 REV. A