













RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680-H,T=0.25mm
PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u"GOLD/TIN PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDERTAILS
50u" NICKEL UNDERPLATING OVERALL
PEG:100u" TIN PLATING ON SOLDERTAILS
50u" NICKEL UNDERPLATING OVERALL

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Brass C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE

GENERL TOLERANCE	
X.±0.30	X.°±3°
.X±0.20	.X°±2°
.XX±0.05	.XX°±0.5°

制图 DRAWING	EMMA		
审核 CHECK	EVA		
核准 APPROVAL	JADE		
单位 UNITS	MM	比例 SCALE	1:1

料号 PART NO.	BX-SATA-02-7PSTG	版本 REV.	A
品名 TITLE	SATA 7P 公座 三面包 SMT型	页次 SHEET	1/1
客户料号 CUTM.NO.			

Bossie（博锡）