








RoHS



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

Product Edge



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD								
BASIC DIMENSION	TOLERANCE	DSND	Q	T	26.09.10	TITLE: TYPE C16P 板上型贴板母座				
	x.x	±0.20	CHKD	Z	F	C	26.09.10	PART NO: TYPE-C 16PIN 2MD		
	x.xx	±0.15	APVD	L	P	J	26.09.10			
	x.xxx	±0.10								
ANGLES	±3°				UNIT:mm		SCALE: 1:1	SIZE: A4	SHEET: 1/1	