








DEFAULT TOLERANCE: ± 0.05

4.2 SHELL: 30u" Min. NICKEL ALL OVER,



Signal Name	GND	SSRXp1	SSRXn1	V _{BUS}	SBU2	Dn2	Dp2	CC2	V _{BUS}	SSTXn2	SSTXp2	GND
PIN	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
Signal Name	GND	SSTXp1	SSTXn1	V _{BUS}	CC1	Dp1	Dn1	SBU1	V _{BUS}	SSRXn2	SSRXp2	GND
PIN	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12



		版本 VER	A0
---	---	-----------	----

RoHS

目錄
MAPX



设变内容
MODIFICATION

日期
DATE



包装规范说明:

1. 自动机包装前先调整前段空出15格, 中间装300PCS产品, 尾端需空出15格;
2. 按照图示方向将成品一一放入REEL包装盘内, 依同一方向放入;
3. 一个REEL包装盘放置300个成品, 装满成品的REEL盘外圈需装上保护带, 四周贴上美纹胶, 盘面贴一张内标签;
4. 将每盘产品依次放入箱内, 一箱装10盘 (300*10=3000PCS). 四周用三角板固定, 最后用透明胶纸将纸箱四周封实, 箱外贴上外标签;
5. 若有未装满之零数箱, 必须以缓冲材料塞满, 数量比较少时可单盘包装出货;
6. 剥离力0.1-1.3KG(300mm/min), 剥离角度:165°~180°;
7. 适用产品:TYPE C 24PIN直立式H12/13四/六脚用



NO.	包材名称 Items	包材料号 Item no	用量 Usage	适用类别 Series	备注 / Remark
①	纸箱 Carton		1		390*390*400mm
②	三角板 FOLDER PAPER BOARD		4		H30mm W7.0mm*3折
③	载带 carrier tape		8		W=32mm PET 透明L=5.38M
④	保护膜 cover tape				W=25.5MM, 300m/r透明色
⑤	塑胶卷轴 Plastic Reel		10		φ380mm, W=37mm
⑥	干燥剂 Desiccant		4		
⑦	环保标签 RoHS Label		9		
⑧	合格标签 Qualified Label		8		70*60mm
⑨	出货标签 Delivery Label		1		70*60mm

产品图 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE			
X.	±0.35	X'.	±5'
.X	±0.30	.X'	±2'
.XX	±0.25	.XX'	±1'
.XXX	±0.10	.XXX'	±0.5'



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW



版本
VER

A0