



Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage): 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge): AWG#20~#24.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-MX3.0-2-MDZ	版本 REV.	A
			X.±0.30	X.*±5°	审核	EVA	品名 TITLE	MX3.0MM TERMINAL	页次 SHEET	1/1		
					CHECK							
					核准						JADE	客户料号 CUTM.NO.
APPROVAL												
			.XX±0.15		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			