






SECTION:Y-Y



PCB LAYOUT
TOLERANCES:±0.05MM

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u",3u",5u",15u"GOLD PLATING
ON CONTACT AREA

100u" MIN.TIN PLATING ON SOLDER TAILS

40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C

4.THE MARK DIMENSIONS MUST BE MEASURED BY FAI.

环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-01-22PSTG	版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X.±0.30	X.*±3°	审核 CHECK	EVA		品名 TITLE	SATA7+15P公座沉板线SMT H0.9 (半包式)	页次 SHEET	1/1
2	Terminal	Brass C2680		Gold/Tin Plated				.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX*±0.5°		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK												