






适用线路板(PCB LAYOUT)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V AC, DC.
4. 耐电压: 500V AC/minute.
5. 接触电阻: $\leq 20\text{m}\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 1.5A AC, DC.

Part No	CKT	A	B	C	D
BX-MX1.2-1-2PWT-1U	2	4.20	1.20	2.65	3.64
BX-MX1.2-1-3PWT-1U	3	5.40	2.40	3.85	4.84
BX-MX1.2-1-4PWT-1U	4	6.60	3.60	5.05	6.04
BX-MX1.2-1-5PWT-1U	5	7.80	4.80	6.25	7.24
BX-MX1.2-1-6PWT-1U	6	9.00	6.00	7.45	8.44

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-MX1.2-1-NPWT-1U	版本 REV.	A
①	1.2 Pitch B型2代电池座胶芯	LCP UL94 V-0 颜色:黑色				X.±0.30	±1°	审核 CHECK	EVA		品名 TITLE	1.20 Pitch B型卧式2代电池座	页次 SHEET	1/1
②	1.2 Pitch B型2代电池座端子	铜合金/表面镀金				.X±0.20		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
③	1.2 Pitch B型2代电池座焊片	铜合金/表面镀金				.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)		