





CIRCUIT DIAGRAM



- TECHNICAL PARAMETERS
- 1.RATED CURRENT: 50MA AT 12V DC
 - 2.CONTACT RESISTANCE: 100 MΩ (MILLIOHMS)
 - 3.TRAVEL: 0.2±0.1 MM
 - 4.INSULATION RESISTANCE: 100 MΩ (MEGOHMS) MIN.
 - 5.WITHSTANDING VOLTAGE: 250V AC, 50HZ, FOR 1 MINUTE

E	COVER PLATE	1	BRASS	COPPER-TIN PLATED	
D	PUSH BUTTON	1	LCP	WHITE	
C	CONTACT SPRING	1	SUS		
B	BASE HOUSING	1	PPA	CLEANED	
A	RETAINER CLIP	1	BRASS	Ag PLATING	
NO	NAME	NUMBER	MATERIAL	ELECTRIC PLATING	REMARKS



PART NO:TC-3603C-H-XXX

H=2.5 160--160gf

H=3.0 260--260gf

PCB HOLES(TOP VIEW)

GENERAL TOLERANCE:±0.05mm

按力	160±30gf	260±50gf
寿命	3万次	3万次

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD			
BASIC DIMENSION	TOLERANCE	DSND	H J	2026.03.28	TITLE:TACT SWITCH
>0.5-2	±0.1	CHKD	Y H C	2026.03.28	PART NO:TC-3603C-H-XXX
>2-5	±0.20	APVD	L P J	2026.03.28	
>5以上	±0.30				
ANGLES	±1°	UNIT:mm	SCALE:1:1	SIZE:A4	SHEET:1/1