







通用线路板(PCB LAYOUT)



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V AC, DC.
4. 耐电压: 500V AC/minute.
5. 接触电阻: $\leq 20\text{m}\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 1.5A AC, DC.

Part No	CKT	A	B	C	D
BX-MX1.2-1-2PWT	2	4.20	1.20	2.65	3.64
BX-MX1.2-1-3PWT	3	5.40	2.40	3.85	4.84
BX-MX1.2-1-4PWT	4	6.60	3.60	5.05	6.04
BX-MX1.2-1-5PWT	5	7.80	4.80	6.25	7.24
BX-MX1.2-1-6PWT	6	9.00	6.00	7.45	8.44

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-MX1.2-1-NPWT		版本 REV.	A	
						X.±0.30	±1°	审核 CHECK	EVA			品名 TITLE	1.20 Pitch B型卧式2代电池座		页次 SHEET	1/1	
								.X±0.20	核准 APPROVAL	JADE			客户料号 CUTM.NO.	 Bossie (博锡)			
										.XX±0.10	单位 UNITS	MM	比例 SCALE				
①	1.2 Pitch B型2代电池座胶芯	LCP UL94 V-0 颜色:黑色															
②	1.2 Pitch B型2代电池座端子	铜合金/表面镀锡															
③	1.2 Pitch B型2代电池座焊片	铜合金/表面镀锡															
1		2		3		4		5		6		7		8		9	