





RoHS

MAPX


MODIFICATION

DRW

DATE



接点定义放大图 (16P)



备注:

- 电气测试:
 - 1接触抗阻: 30m Ω MAX, 寿命后变化 $\pm$ 10m Ω
 - 2耐电压: 100V AC
 - 3绝缘阻抗: 1000M Ω MIN
 - 4额定电流 5A
- 机械测试:
 - 2.1耐久测试: 10000次;
 - 2.2插入力: 20N Max;
 - 2.3拔出力: 8N Min;
- 包装:
 - 3.1 PE袋包装, 最小包装量1000PCS
- 环境:
 - 4.1工作温度: -55 $^{\circ}$ C~+88 $^{\circ}$ C

产品图

PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

X.	$\pm$ 0.35	X.	$\pm$ 5. $^{\circ}$
.X	$\pm$ 0.25	.X	$\pm$ 2. $^{\circ}$
.XX	$\pm$ 0.20	.XX	$\pm$ 1. $^{\circ}$
.XXX	$\pm$ 0.05	.XXX	$\pm$ 0.5 $^{\circ}$

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	L-S-S	制图料号 PRODUCT PART NO.	918-418K2027E40006
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	TYPE-C3.1母座无边夹板1.0 长度7.3LCP黑胶16PIN新模
日期 DATE	2021-03-10	核准 APPD	黄国荣	角法 VIEW	版本 VER
					A0