






RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATE

RECOMMENDED PCB LAYOUT



电气特性:Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗: Contact Resistance
30 milliohms MAX
- 耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 绝缘阻抗: Lnsulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

- 插拔力: Cnnector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
- 端子保持力: Terminal Retenion
1.0kgf (MIN)
- 寿命: 1500次

原材料: Matorial:

- 塑胶: Housing: pbt /lcp
- 端子: Contact: Copper Alloy C2680
- 外壳: Shell: SPCC/c2680

电镀: Finish:

- 端子 Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
- 外壳 Shell: Nickel 50u" Min plating over all.
- Temperature Range: -55° C to +85° C

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

产品图 PRODUCT CHART DWG					
公差一览表 TOLERANCE UNLESS OTHERWISE					
X.	±0.35	X'.	±5°		
.X	±0.30	.X"	±2°		
.XX	±0.25	.XX"	±1°		
.XXX	±0.10	.XXX"	±0.5°		

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	909-261A1015D10102
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	AF90度10.0短体后两脚无边铁壳PBT白胶7.2
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	版本 VER
					A0