













SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:C2680R-H,T=0.50mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA

100u"TIN PLATING ON SOLDERTAILS

30u"NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u"NICKEL UNDERPLATING OVER ALL



RECOMMENDED PCB LAYOUT

PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE

GENERL TOLERANCE		
X.	±0.30	X.° ±5°
X.X	±0.20	X.X° ±3°
X.XX	±0.10	X.XX°±2°

制图 DRAWING	ROSE		
审核 CHECK	LEO		
核准 APPROVAL	JOHN		
单位 UNITS	MM	比例 SCALE	1:1

料号 PART NO.	ZX-SATA-02-22PSZM	版本 REV.	A
品名 TITLE	SATA 7+15P 母座 DIP 180° 双排双色叉加长型针长2.7	页次 SHEET	1/1
客户料号 CUTM.NO.			

兆星精密电子（深圳）有限公司

ShenZhen ZhaoXing Precision electronics Co., Ltd.