



A



SECTION A-A
SCALE 1:1

Specifications

A. Material

Insulator: LCP, UL94 V-0, Black
Contact: Copper Alloy, T=0.12mm
Mid Plate: Stainless Steel, T=0.15mm
Shell: Stainless Steel, T=0.30mm
EMI: Stainless Steel, T=0.10mm

B. Plating

Contact Area: 3u" Au over 60u" min. Nickel
Solder Tails: Gold Flash Au over 60u" min. Nickel
Shell: 60u" min. Nickel
EMI: 50u" min. Nickel
Mid Plate: 40u" min. Matte Tin over 30u" min. Nickel




C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins
Voltage Rating: 48V
Power Rating: 240W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.


D. Mechanical & Environmental

Operating Temperature: -25°C to +85°C
Mating Force: 5 to 20 N.
Unmated Force: 6 to 20 N after test
Durability: 10,000 cycles

B



C



D


E

Part Number			Product Description			
PTCFW-H22F-004			USB 3.2 Gen 2 Type C Receptacle, Horizontal, Dual Row SMT, Mid Mount, 1.0mm Offset, 24 Pin			
DWG.No.	P-TCF-064		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X	±0.35	X°	±5°
Designed	Lee	11/25/20	X.XX	±0.25	X.X°	±2°
Approved	Allen	11/25/20	X.XXX	±0.15		




www.szywf.com.cn
www.szywf.cn

Sheet No. 1/3



RECOMMENDED PCB LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05



PIN ASSIGNMENTS


PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TX1+	B11	RX1+
A3	TX1-	B10	RX1-
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RX2-	B3	TX2-
A11	RX2+	B2	TX2+
A12	GND	B1	GND

Part Number			Product Description			 <i>Connecting the Future</i> www.szywf.com.cn www.szywf.cn
PTCFW-H22F-004			USB 3.2 Gen 2 Type C Receptacle, Horizontal, Dual Row SMT, Mid Mount, 1.0mm Offset, 24 Pin			
DWG.No.	P-TCF-064		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X ±0.35	X° ±5°	 ROHS COMPLIANT 2011/65/EU Deca-BDEV	
Designed	Lee	11/25/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	11/25/20	X.XXX ±0.15			
						Sheet No. 2/3






www.szywf.com.cn
www.szywf.cn


Sheet No. 2/3



SEE DETAIL X



	REEL	CARTON
QUANTITY (PCS)	900	9000

Part Number			Product Description				 Connecting the Future www.szywf.com.cn www.szywf.cn	
PTCFW-H22F-004			USB 3.2 Gen 2 Type C Receptacle, Horizontal, Dual Row SMT, Mid Mount, 1.0mm Offset, 24 Pin					
DWG.No.	P-TCF-064		Tolerances Unspecified			Units: Metric(mm)		
Revision	A0		X.X ±0.35	X° ±5°				
Designed	Lee	11/25/20	X.XX ±0.25	X.X° ±2°				
Approved	Allen	11/25/20	X.XXX ±0.15					
							Sheet No. 3/3	