

ROHS Compliant

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012/03/28	NEW	CALM

NOTES:

Voltage Rating: 100V, AC/DC

Current Rating: 1.0 AMP, AC/DC

Dielectric Withstand Voltage: 500V, AC/Minute

Contact Resistance: 20 mΩ Max






Insulation Resistance: 1000 mΩ Min

Operation Temperature: -40°C to +105°C

Insulator Material: Polyester (LCP), UL94 V-0

Contact Material: Brass

Contact Plating: Au Plated on Nickel Overall



Recommended P.C.B Layout
P.C.B Board Tolerance ±0.05

Dimension antitheses list				
item	PA	PB	W	L
Standard	3.00	3.00	5.85	7.88
Alternate	---	---	---	---



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

UNIT mm OPERATION X.X ±0.40 X.XX ±0.25 X.XXX ±0.15 Angle ±3° DIM TOL	PRODUCT NAME :	1.27mm Pin Header H=2.5, Dual Row, 180°SMT	DRAW:	Calm	DATE:	2012/03/28
	DRAWING NO. :	1125-205MG0B079R1	CHECK:		DATE:	
	PRODUCT NO. :	1125-205MG0B079R1	APPROVED:		DATE:	
	PROJ.	SCALE	1:1	SHEET	1/1	