





SECTION A-A
SCALE 1:1



Specifications

A. Material

Insulator: LCP, UL94 V-0, Black
Contact: Copper Alloy, T=0.15mm
Mid Plate: Stainless Steel, T=0.30mm
EMI Plate: Stainless Steel, T=0.10mm
Shell: Stainless Steel, T=0.15mm

B. Plating

Contact Area: 3u" Au over 50u" min. Nickel
Solder Tails: 100u" min. Matte Tin over 50u" min. Nickel
Shell: 30u" min. Nickel
EMI: No Plating
Mid Plate: 80u" min. Matte Tin over 50u" min. Nickel


C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins
Voltage Rating: 48V
Power Rating: 240W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental

Operating Temperature: -25°C to +85°C
Mating Force: 5 to 20 N.
Unmated Force: 6 to 20 N after test
Durability: 10,000 cycles





Part Number			Product Description			
PTCMW-H12B-003			USB 3.2 Gen2 Type C Plug, Vertical, SMT, 24 Pin			
DWG.No.	P-TCM-091		Tolerances Unspecified		Units:	
Revision	A0		X.X ±0.35	X° ±5°	Metric(mm)	
Designed	Lee	11/18/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	11/18/20	X.XXX ±0.15			



RECOMMENDED PCB LAYOUT (COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05

PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TX1+	B11	RX1+
A3	TX1-	B10	RX1-
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RX2-	B3	TX2-
A11	RX2+	B2	TX2+
A12	GND	B1	GND




Part Number			Product Description		
PTCMW-H12B-003			USB 3.2 Gen2 Type C Plug, Vertical, SMT, 24 Pin		
DWG.No.	P-TCM-091		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ± 0.35	X° $\pm 5^\circ$	
Designed	Lee	11/18/20	X.XX ± 0.25	X.X° $\pm 2^\circ$	
Approved	Allen	11/18/20	X.XXX ± 0.15		






www.szywf.com.cn
www.szywf.cn

Sheet No. 2/3




SEE DETAIL X



	REEL	CARTON
QUANTITY (PCS)	400	4000

Part Number			Product Description		
PTCMW-H12B-003			USB 3.2 Gen2 Type C Plug, Vertical, SMT, 24 Pin		
DWG.No.	P-TCM-091		Tolerances Unspecified		
Revision	A0		X.X ±0.35	X° ±5°	
Designed	Lee	11/18/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	11/18/20	X.XXX ±0.15		

Units:
Metric(mm)



ROHS
COMPLIANT
2011/65/EU
Deca-BDEV



www.szywf.com.cn
www.szywf.cn

Sheet No. 3/3