


Rating: 0.5A 30V DC
Contact Resistance: 100 mΩ Max.
Operating temperature: -20℃~70℃
Operating force: 3~20N
Operating Life: 5,000cycles

③	Housing	_____	1	THERMOPLASTIC	Black	_____
②	Shell	_____	1	SUS	Plating Nickel	_____
①	Terminal	_____	2	Phosphor bronze	Plating silver	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE			
DRAWN	JKUN.LU	2019/11/11				
CHECKED						
APPROVALS				TITLE:	PHONE JACKES	
				PART NO.	PJ-399-6A	
TOLERANCES ARE		30~以上	+0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	+0.20			
		5~10	+0.15			
		~ 5	+0.10			
		±2°	DRAWING NO.	_____	SHEET 1 OF	

	A		NEW	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHECK. APPRO.