








技术参数:

1. 做用温度: $-25\sim+85^{\circ}\text{C}$;
2. 额定负荷: DC 12V 50mA;
3. 接触电阻: $\leq 50\text{m}\Omega$;
4. 绝缘电阻: $\geq 100\text{M}\Omega$;
5. 耐 压: AC250V (50Hz)/min;
6. 动 作 力: $260\text{g}\pm 50\text{g}$;
7. 使用寿命: 100000次;



高度L	帽头H	直径A
3.15	4.3	Ø3.5
3.85	5.0	Ø3.5
4.85	6.0	Ø3.3
5.35	6.5	Ø3.3
6.35	7.5	Ø3.3
7.35	8.5	Ø3.2
7.85	9.0	Ø3.2
8.35	9.5	Ø3.1
11.85	13.0	Ø3.0
19.35	21.0	Ø3.0

Ordering Information

TC - 6616 * - NH - *G - ** - F* * - 02

系列号 F=防水 CV=护套 SQ=方头 P=带柱 按钮高度 动作力 中心高度 脚长 默认=8脚 Z=直脚

5	接触脚	H62Y 黄铜	镀银	2	T=0.30
4	基座	PPA(黑色)	———	1	
3	簧片	不锈钢	镀银	1	
2	支架	冷轧钢带	铜锡	1	
1	按钮	PPA(黑色)	———	1	
序号	零件名称	材料规格	表面处理	数量	备注

			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	轻触开关(机架式 卧插 6.15x7.5mm 中心高度6.0 脚长3.0)	版 本 REV.	A
			X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	TC-6616-NH-260G-6.0-F3.0-02	单 位 UNITS	mm
1	初版发行		X. XXX	±0.10	投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°					