
SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2022.08.17



Technical Specifications

1. Frequency Range: 0 ~ 6 GHz
2. Impedance: 50 Ω
3. VSWR (Voltage Standing Wave Ratio): ≤ 1.35
4. Operating Voltage: 335 V
5. Withstand Voltage: 1000 V
6. Insulation Resistance: ≥ 5000 MΩ
7. Contact Resistance:
   Inner Conductor ≤ 3 mΩ
   Outer Conductor ≤ 2 mΩ
8. Insertion Loss: ≤ 0.5 dB
9. Tolerance for all unspecified dimensions: ±0.2

SMA-JJ-212-L0-0

- Surface treatment镀层:镀金
- Method:垂直转接公头双针
- Length体长:21.2mm
- Product number编号:JJ系列
- Product series系列:SMA同轴射频天线座

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
C	导针	黄铜	1	镀金					
C	插孔	HPB59-1	1	------				GENERAL TOLERANCE	
B	绝缘体	聚四氟乙烯	1	------				≥0~2<	±0.15
A	主体	黄铜	1	镀金	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.SANCNN.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: SMA内螺内针
转内螺内针 双针 SMA转接头

DWG NO：SMAJJ-P0021

PART NO：SMAJJ-11075

MODEL NO：SMA-JJ-212-L0-0

NAME： SMA
COAXIAL RF CONNECTOR