SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12







Technical Specifications
1.Frequency range: 0~6 GHz
2.Impedance: 50 Ω
3.VSWR (Voltage Standing Wave Ratio): ≤1.5
4.Operating voltage: 335 V
5.Dielectric withstand voltage: 1000 V
6.Insulation resistance: ≥5000 MΩ
7.Contact resistance: inner conductor ≤3 mΩ, outer conductor ≤2 mΩ
8.Insertion loss: ≤0.5 dB
9.Tolerance for unspecified dimensions: ±0.2
10.Standards: MIL-C-39012, IEC169-15, CECC22110

SMA-KE-108-S4-0

- Surface treatment镀层:普金
- Pin position脚位:S4-SMT正脚4pin
- Length体长:10.8mm
- Product number编号:KE
- Product series系列:MSA同轴射频天线座



PCB LAYOUT

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR
C	插孔	HPB59-1	1	------
B	绝缘体	聚四氟乙烯	1	------
A	主体	黄铜	1	镀金

DESIGN	WANGGUIFA	2018.06.12
CHECKED	ZHENGUILAN	2018.06.12
APPROVED	LILIANJIANG	2018.06.14

GENERAL TOLERANCE	
≥0~2<	±0.15
≥2~5<	±0.25
≥0~2<	±0.15
≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.SANCNN.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: SMA-KE10.8正脚4P 立贴
DWG NO：SMAKE108-P001
PART NO：SMAKE-1900622
MODEL NO：SMA-KE-108-S4-0
NAME： SMA COAXIAL RF CONNECTOR