SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2022.08.17



Technical Specifications

1. Frequency Range: 0 ~ 6 GHz
2. Impedance: 50 Ω
3. VSWR (Voltage Standing Wave Ratio): ≤ 1.5
4. Operating Voltage: 335 V
5. Withstand Voltage: 1000 V
6. Insulation Resistance: ≥ 5000 MΩ
7. Contact Resistance:
   Inner Conductor ≤ 3 mΩ
   Outer Conductor ≤ 2 mΩ
8. Insertion Loss: ≤ 0.5 dB
9. Tolerance for all unspecified dimensions: ±0.2

SMA-JKW-157-T0-0

- Surface treatment镀层:镀金
- Method:90° 公转母头
- Length体长:15.7/15.0mm
- Product number编号:JKW系列
- Product series系列:SMA同轴射频天线座

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR
C	导针	黄铜	1	镀金
C	插孔	HPB59-1	1	------
B	绝缘体	聚四氟乙烯	1	------
A	主体	黄铜	1	镀金

DESIGN	WANGGUIFA	2018.06.12
CHECKED	ZHENGUILAN	2018.06.12
APPROVED	LILIANJIANG	2018.06.14

GENERAL TOLERANCE	
≥0~2<	±0.15
≥2~5<	±0.25
≥0~2<	±0.15
≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.SANCNN.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: SMA-JKW天线转接头
L型90度直角弯头 公转母

DWG NO：SMAJKW-P0001

PART NO：SMAJKW-0015

MODEL NO：SMA-JKW-157-T0-0

NAME： SMA
COAXIAL RF CONNECTOR