





Kinghelm®



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/	新版发行	24.12.20	



3 Pin以上



2 Pin



材料及电镀

- ①. 螺 丝: M2.5, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 夹 子: 磷青铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍
- ⑤. 塑件盖板: PA66, UL94V-0

电气性能

额定电压: 300V
额定电流: 15A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC2000V\1Min
使用线径: 28-14AWG 2.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.5Nm(4.43Lbin)
剥线长度: 7-8mm

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

公差参数:

Poles	Dim	Dim P	Dim L
2-6P	±0.10	±0.20	
7-12P	±0.20	±0.30	
13-18P	±0.25	±0.40	
19-24P	±0.30	±0.50	

未注明公差:

X. xxx ±0.10
X. xx ±0.20
X. x ±0.30

NAME:

5.08接线端子公头

P/N: KH-ZBK400R-**P-5.08GS-1
(*代表P数)

DWG NO:

THIRD ANGLE PROJECTION



UNIT:	SCALE	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A1

DRAWN:

CHECKED:

APPROVED: