






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/	新版发行	24.12.20	



SECTION A-A



材料及电镀

- ①. 螺 丝: M2.0, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 夹 子: 磷青铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍
- ⑤. 塑件盖板: PA66, UL94V-0

电气性能

额定电压: 300V
额定电流: 8A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC1000V
耐 电 压: AC1500V\1Min
使用线径: 24-14AWG 0.5-1.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.2N.m (1.77Lb. in)
剥线长度: 6-7mm

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

NAME:

接线端子3.81 单排 封闭公头

P/N:

KH-ZBK200R-**P-GS-1 (**代表P数)

DWG NO:

THIRD ANGLE PROJECTION



UNIT:	SCALE	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A1

DRAWN:

CHECKED:

APPROVED: