




RoHS Compliant



PIIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
CD	Detect Switch
C5	GND
C6	VPP
C7	I/O



RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05  SMT SOLDER AREA

 COPPER RESTRICTED AREA
1. TOUCH AREA OF CONTACT
TIPS NO ELECTRICAL FUNCTION
2. NO FIRST PCB_LAYOUT
CIRCUITS IN THE AREA

MEASURE POINT:	
QUADRANT POINT	☐ QP
TANGENCY POINT	☐ TP
INTERSECTION POINT	☐ IP

UNLESS OTHERWISE SPECIFIED, TOLERANCE:	
X.	± 0.25
X.x	± 0.20
X.xx	± 0.15
ANGULAR	$\pm 3^{\circ}$

LCK-NANO-113B-P7-H137-Y-L-G

- LCK-NANO-113B**
 - LCK: 连晟欣
 - NANO: 产品类别
- P7**
 - 7PIN: 产品PIN位
- H137-Y**
 - H150: 产品高度
 - Y: 有柱
- L**
 - L: 有柱无柱
 - L: 圆盘
- G**
 - G1: 电镀规格
 - G3: 以此类推
 - G: 包装方式

Notes:

1.Material:
Housing: High Temperature Thermoplastic
Terminal:Copper Alloy
Shell: Stainless Steel

2.Plating:
Terminal:50u" Ni Underplated Overall
G/F Plated On Contact Area
G/F Plated On Solder Area
Shell:30u" Ni Underplated Overall
G/F Plated On Contact Area And Solder Area

3.Technical Speciality:
Rated Voltage: 30V
Current Rating: 0.5A
Insulation Resistance:1000M Ω Min.
Contact Resistance:100m Ω Max.
Withstanding Voltage: 500V DC For 1 Minutes.
Operating Temperature: -40 $^{\circ}$ ~+75 $^{\circ}$ Humidity 80% R.H Max.

卡片尺寸
2:1

3D VIEW

 联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE: 137H NANO SIM CARD CONNECTOR 防飞自锁结构		
CHECKED		DATE				
APPROVED		DATE				
PART NO: LCK-NANO-113B-P7H137-YLG				REV: 04	SCALE: 1:1	UNIT: mm
DRAWING NO:				SIZE: A4	SHEET: 1/1	