







技术指标:

1. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压: 200V AC, DC.
3. 耐电压: 200V AC/minute.
4. 接触电阻: $\leq 25\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 2A AC, DC.



CKT	A	B	C
2	2.00	4.50	5.70
3	4.00	6.50	7.70
4	6.00	8.50	9.70
5	8.00	10.50	11.70
6	10.00	12.50	13.70
7	12.00	14.50	15.70
8	14.00	16.50	17.70
9	16.00	18.50	19.70
10	18.00	20.50	21.70
11	20.00	22.50	23.70
12	22.00	24.50	25.70
13	24.00	26.50	27.70
14	26.00	28.50	29.70
15	28.00	30.50	31.70
16	30.00	32.50	33.70



一般公差 (TOLERANCE)
X ± 0.50 .XX ± 0.10
.X ± 0.20 .XXX ± 0.05
ANGLES $\pm 1^{\circ}$

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

品名 (TITLE)	PH2.0 WTB公头胶壳	制图 (DR)	ANLAN
料号 (DWG.NO)	KH-PH-NP-JK	校对 (CHKD)	李绍宗
比例 (SCALE)	1:1	审核 (APPD)	黄志明
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
尺寸 (SIZE)	A4	REV	A