




NOTE

1. SPECIFICATIONS

WITHSTANDING VOLTAGE: 500V AC

CURRENT RATING: 2AMP

INSULATION RESISTANCE: 1000M Ω MIN

CONTACT RESISTANCE: 20 m Ω MAX

TEMPERATURE RANGE: -55° C ~ +85° C

2. MATERIAL

HOUSING: THERMOPLASTIC UL94V-0

CONTACT: BRASS

3. FINISH: SEE TABLE

Table:

PART NAME	Q'TY	Material
CONTACT	1	C2680R-H, NI 80U"
HOUSING	1	PBT+30%GF, BLACK
CONTACT	1	C2680R-H, GOLD FLASH
CONTACT	1	C2680R-H, GOLD 15U"
CONTACT	1	C2680R-H, GOLD 30U"
CONTACT	1	C2680R-H, 半金镍 0.4U"

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
.X $\pm$ 0.30	$\pm$ 1°	PART NO. HMT-254D-2-KB	TITLE: 2.54mm 开口短路帽	
.XX $\pm$ 0.20				
.XXX $\pm$ 0.10		DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SCALE N:A
				SHEET 1/1