






RoHS
Compliant



REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



P.C.B LAYOUT VIEW TOLERANCE ± 0.05

SPECIFICATION:





1.ELECTRICAL CHARACTERISTICS:

- 1.1 CURRENT RATING: 5A
- 1.2 TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$
- 1.3 CONTACT RESISTANCE: 30 MILLIONHM MAX.
- 1.4 DIELECTRIC WITHSTANDING VOLTAGE: 100 VAC r.m.s
- 1.5 INSULATION RESISTANCE: 100 MEGOHMS MIN.

2.MECHANICAL CHARACTERISTICS

- 2.1 INSERTION FORCE: 5~20N
- 2.2 EXTRACTION FORCE: Initial:8~20N,ATER TEST 6~20N
- 2.3 DURABILITY:10,000CYCLES

3.THE SHELL LENTH IS LESS THAN THE MINIMUM SPECIFIED BY THE USB TYPE C STANDARD.AS SUCH IS CONNOT INDENOENDENTLY BE GUARANTEED TO MEET ALL TYPE C MECHANICAL REQUIREMENTS.








PIN ASSIGNMENT													
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	BLADE	SHELL
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND		
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND		
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	GND	GND

2	IM_HOUSING	1 PCS	High Tep. Plastic+Copper alloy+Stainless Steel	Au & Ni Plated
1	SHELL	1 PCS	Stainless Steel	Ni Plated
NO.	DESCRIPTION	QTY.	MATERIAL	FINISHED
X.	± 0.50	X.* $\pm 2^{\circ}$	UNITS	广东创粤科技有限公司
.X	± 0.30	.X.* $\pm 1^{\circ}$	mm	
.XX	± 0.10	.XX.* $\pm 0.5^{\circ}$	MAT'L	
.XXX	± 0.05			
			FINISH	TITLE:
			Q'TY	TYPE-C 16PIN板上四脚插板SMT母座 L=5.15MM 舌片外露1.15MM
			CHKD:	TYPE-C-16P-L5.15SMT-26908 DWG NO.:
			DR:	
				SCALE SHEET REV.
				1/1 1/1 A1



RoHS
Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



- NOTES 2:
- MATERIAL:
 - REEL AND AXLE: PS,BLUE
 - CARRIER TAPE: PET, LUCID
 - COVER TAPE: PS,TRANSPARENT
 - SHIPPING CARTON: CORRUGATED FIBER
 - DIMENSION:
 - REEL: W=24.5, $\phi A=330$
 - CARRIER TAPE: T=0.30 W=24.0
 - COVER TAPE: T=0.05 W=21.5
 - SHIPPING CARTON: L=335mm, W=335mm, H=425mm
 - QUANTITY :
 - PRIMAY PACKING: 1200PCS/REEL
 - SECONARY PACKING: 12 REELS/CARTON(14400PCS/CARTON)
 - PEELING RESISTANCE: 0.1~1.3N
 - PEELING SPEED: 300mm/minutes
 - PEELING ANGLE: 165° ~180°

X. ±0.50	X* ± 2°	UNITS	广东创粤科技有限公司		
.X ±0.30	.X* ± 1°	mm			
.XX ±0.10	.XX* ± 0.5°	MAT'L	TITLE:		
.XXX ± 0.05			TYPE-C 16PIN板上四脚插板SMT母座 L=5.15MM 舌片外露1.15MM		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD:	DWG NO.:	
			CHKD:		
		Q'TY	DR:		
					SCALE SHEET REV.
				1/1	1/1 A1