





技术指标 (Technical Index):

1. 工作温度 (Temperature range): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压 (Rated voltage): 50V DC/AC(rms).
3. 额定电流 (Rated current): 1.5A, AC/DC (AWG#28).
4. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值 (Dielectric withstanding voltage): 500V AC/minute.
6. 绝缘电阻 (Insulation resistance): $\geq 100\text{M}\Omega$.
7. 适用线规 (Apply to gauge): AWG28#~AWG30# (0.5mm~0.7mm).

P/N	材质	镀层
WF-MX1.2-DD2	磷青铜	镀金1u"
WF-MX1.2-DD1		镀锡

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.50	±1°	PART NO. WF-MX1.2-DDX	TITLE: 1.2Pitch B型电池座公头端子		
X.X±0.20			CUSTOMER	SIZE	UNITS
X.XX±0.10		DESIGN: James		A4	MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1