

1 2 3 4 5 6 7 8

H

G

F




E

D

C

B

A



NOTE:

Technical data:

Insulator body:PBT+15% G. F UL94-V0

Curent Rating:3 AMP

Insulator resistance:1000 Megohms min

Dielectric withstanding:AC/DC 500V.

Contact Resistance:25mΩ

Contactmaterial:Bronze.

plating:Gold or tin over nickel

Operating Temperature:-40° C to +105° C

GENERAL TOLERANCES
UNLESS SPECIFIED

.X±0.25
.XX±0.20
.XXX±0.10

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-200D-2-KB
DESIGN: James

CHED: Talen
APPD: Sophia

TITLE:
MJ PH2.0 H:3.5

CUSTOMER
SIZE A4
UNITS MM
SCALE N:A
SHEET 1/1

1 2 3 4 5 6 7 8