




SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40° c to +105° c


Contact Material:Brass

Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard:PBT

Max.Processing Temp:180° C for 30-60 seconds
(200° C for 10 seconds)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	±1°	PART NO. HMT-200D-2-BB	TITLE: 2.00 Mini Jumper 1*2Pin Close Type	
.XX±0.20				
.XXX±0.10		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		A4
		APPD: Sophia		UNITS MM
			SCALE	SHEET
			N:A	1/1