






AFTER ASSEMBLY




A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		





NOTES:

- MECHANICAL: MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.
- ELECTRICAL:
CURRENT: 3.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES
- ENVIRONMENTAL:
OPERATING TEMPERATURE RANGE -30° C ~ +80° C
- Salt Spray: 24H


序号		名称		材料规格					
1		Terminal		C2680 T=0.15mm 电镀金1u" Ni:50u"					
2		卡勾		SUS301 3/4H T=0.15mm 素材					
3		Molding 3		LCP 黑色 UL94 V-0					
4		Shell		SUS201 1/4H T=0.30mm Ni:50u"					
X. ±0.50		X.* ± 2*		UNITS		深圳市创粤科技有限公司			
.X ±0.30		.X* ± 1*		mm					
.XX ±0.10		.XX* ± 0.5*		MAT'L					
.XXX ±0.05									
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD				FINISH		TITLE:			
						TYPE-C 16PIN板上四脚插板SMT母座 长L=6.50MM			
				TYPE-C-16P-3AL6.5-34011		DWG NO.:			
				CHKD:					
				Q'TY		DR:			
						SCALE	SHEET	REV.	
						1/1	1/1	A	



REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



10卷/每箱



X. ± 0.50	X.* ± 2°	UNITS	深圳市创粤科技有限公司			
.X ± 0.30	.X* ± 1°	mm	TITLE:			
.XX ± 0.10	.XX* ± 0.5°	MAT'L	TYPE-C 16PIN板上四脚插板SMT母座 长L=6.50MM			
.XXX ± 0.05		FINISH	APPD:	DWG NO.:		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		Q'TY	CHKD:			
			DR:			
				SCALE	SHEET	REV.
				1/1	1/1	A1