





REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



NOTES:

1. MECHANICAL: MATING FORCE: 5-20N .

UNMATING FORCE: 8-20N .

DURABILITY: 10000 CYCLES MIN.

2. ELECTRICAL:

CURRENT: 3A/5.0A MAX

VOLTAGE: 20V MAX

WITHSTANDING VOLTAGE: 100V AC

CONTACT RESISTANCE: 40 mΩ MAX INITIAL;

50 mΩ MAX AFTER 10000 CYCLES

3. ENVIRONMENTAL:

OPERATING TEMPERATURE RANGE -30° C ~ +80° C

4. Salt Spray: 24H/48H

X. ±0.50	X.* ± 2°	UNITS	深圳市创粤科技有限公司	
.X ±0.30	.X.* ± 1°	mm		
.XX ±0.10	.XX.* ± 0.5°	MAT'L	TITLE:	
.XXX ±0.05			TYPE-C 16PIN板上四脚插板SMT母座 长L=7.35MM 带弹 3MD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD			TYPE-C-16P-L7.35SMT-31436	DWG NO.:
			CHKD:	
			Q'TY	
			DR:	
				SCALE/SHEET REV.
				1/1 1/1 A1

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME