





A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NOTES:

SPECIFICATION:

- CURRENT RATING: 5A MAX
- VOLTAGE: 100 VAC
- TEMPERATURE RANGE: -30 ° C ~ 85 ° C
- CONTACT RESISTANCE: 40 MILLIONHM MAX
- INSULATION RESISTANCE: 100 MEGOHMS MIN.
- INSERTION FORCE : 5N~20N
- UNMATING FORCE: 8N~20N
- DURABILITY: 5000 CYCLES

X. ±0.50	X.* ± 2°	UNITS	深圳市创粤科技有限公司		
.X ±0.30	.X.* ± 1°	mm	TITLE:		
.XX ±0.10	.XX.* ± 0.5°	MAT'L	TYPE-C 16PIN板上后两脚插板SMT母座 长L=7.35MM		
.XXX ± 0.05		FINISH	TYPE-C-16P-L7.35SMT-31439 DWG NO.:		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD			CHKD:		
			Q'TY		
			DR:	SCALE	SHEET
				1/1	1/1
				A1	REV.