










REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

NOTES:

- 1.Material:SEE TABLE1;
- 2.Plating specification,
 - 2-1.Contact:
Contact area: Ni50u"Min/Au ;
Solder area: Ni50u"Min/Sn100u"Min.
Other area: Ni 50u"Min.
 - 2-2.Shell: Ni50u"~150u";
 - 2-3.Latch:
Solder area: Ni50u"Min/Sn100u"Min.
Other area: Ni 50u"Min.
- 3.Mechanical Performance ,
 - 3-1.Insertion Force:5~20N;
 - 3-2.Extraction Force:8~20N after 10000 cycles;
 - 3-3.Durability:10000 cycles.
- 4.Electrical Performance,
 - 4-1.Insulation Resistance:100M Ω Min.
 - 4-2.Contact Resistance :50m Ω Max.
 - 4-3.Dielectric Strength :100V AC.
 - 4-4.Contact current rating: 3.75A/Pin for vbus and gnd, 1.8A/Pin for all other contact.
- 5.The product accords with ROHS STD.



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X.	± 0.50	X.*	$\pm 2^*$	UNITS	
.X	± 0.30	.X*	$\pm 1^*$	mm	
.XX	± 0.10	.XX*	$\pm 0.5^*$	MAT'L	
.XXX	± 0.05				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD				FINISH	
				Q'TY	

广东创粤科技有限公司			
TITLE:			
TYPE-C 16P板上四脚插板SMT母座 L=7.35MM 无弹 15A大电流			
TYPE-C-16P-L7.35SMT15A-07903		DWG NO.:	
CHKD:			SCALE SHEET REV. 1/1 1/1 A1
DR:			



RoHS
Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

载带卷入方向

后空 (20空格)

1000PCS/每盘

前空 (20空格)

16.0

载带①

固定卷盘胶带

载带保护带⑤

上带②


旋转方向

③ 盘面标签

卷盘④



卷装注意事项:

1. 上带不可盖住载带棘轮孔, 且不可超出载带边缘
2. 产品包在载带中不可放反, 产品不可超出载带高度
3. 载带轻轻翻转过来, 产品能自由落下不卡产品
4. 包装后载带及上带不可有破损, 折皱等不良
5. 盘面标签统一朝载带圆孔的另一面
6. 上带剥离力: 40-100gf



天地板⑥

三角柱⑦



外箱⑧

外标签⑨

装箱示意图

包材组成用量

卷装示意图

ITEM	描述	材质	规格	用量
1	载带	PET	W=16mm T=0.35mm	10
2	上带	PET	W=12.7mm T=0.05mm	10
3	盘面标签			1
4	卷盘	PS	Ø330MM*W20.5MM	10
5	载带保护带			1
6	天地板	B=B	L320mm*W320mm	2
7	三角柱	B=B	L290mm*W210mm	4
8	外箱	K=K	L340mm*W340mm*325mm	1
9	外标签			1

1	板上16P长7.35	1000	10000
序号	品名	每盘数量	每箱数量

X. ±0.50	X.* ±2*	UNITS	广东创粤科技有限公司		
.X ±0.30	.X* ±1*	mm			
.XX ±0.10	.XX* ±0.5*	MAT'L			
.XXX ±0.05					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD			TITLE:	TYPE-C 16P板上四脚插板SMT母座 L=7.35MM 无弹 15A大电流	
			FINISH	APPD:	DWG NO.:
			Q'TY	CHKD:	
				DR:	
					SCALE SHEET REV.
					1/1 1/1 A1