










REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND

特性:

一、电气性能: EICTRICAL

- 1.额定电流: 5.0A
- 2.接触阻抗: 40 MILLIOHMS MAX
- 3.耐电压: 150V AC / 1 mA MAX
- 4.绝缘阻抗: 150V DC/100 MEGA OHMS MIN

二、机械性能:

- 1.插入力: 5~20N
- 2.拨出力: 8~20N
- 3.使用寿命: 10000次、拨出力 5N MIN

三、材料: MATERIAL

- 1.塑胶: LCP黑色 UL94V-0
- 2.端子: C7025 T=0.15MM
- 3.外壳: SUS201/SUS304 T=0.30MM
- 4.卡勾: SUS301 T=0.15MM

四、电镀: FINISH

- 1.端子: 接触点镀金1U"MIN
PIN脚焊接区域镀金1U"MIN.
- 2.外壳: 镀镍80U"MIN

五、电镀品需做粘锡测试: 粘锡面积达到95%以上。








六、SMT回流焊(峰值260°C±5°C)不能起泡、
熔胶、变色不良(变形在公差范围内)

七、工作温度: -30°C~+80°C

X. ±0.50	X* ± 2°	UNITS mm	深圳市创粤科技有限公司
.X ±0.30	.X* ± 1°		
.XX ±0.10	.XX* ± 0.5°	MAT'L	TITLE:
.XXX ± 0.05			TYPE-C 16PIN板上四脚插板SMT母座 长L=8.35MM
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-16P-L8.35SMT-34005 DWG NO.:
		Q'TY	CHKD:
			DR:
			SCALE SHEET REV. 1/1 1/1 A1



REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



10卷/每箱

X. ±0.50	X° ± 2°	UNITS mm	深圳市创粤科技有限公司	
.X ±0.30	.X° ± 1°	MAT'L /	TITLE:	
.XX ±0.10	.XX° ± 0.5°		TYPE-C 16PIN板上四脚插板SMT母座 长L=8.35MM	
.XXX ± 0.05		FINISH /	APPD:	DWG NO.:
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD.		Q'TY /	CHKD:	SCALE SHEET REV.
			DR:	1/1 1/1 A1