









A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X.	±0.50	X.*	± 2°
.X	±0.30	.X*	± 1°
.XX	±0.10	.XX*	± 0.5°
.XXX	± 0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD.

UNITS	mm
MAT'L	
FINISH	
Q'TY	

深圳市创粤科技有限公司	
TITLE:	TYPE-C 16PIN沉板0.8MM母座 长L=6.50MM
TYPE-C-16P-R0.8L6.5-34002	DWG NO.:
CHKD:	
DR:	
SCALE	SHEET
1/1	1/1
REV.	A1




- NOTES:
- MECHANICAL:MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.
 - ELECTRICAL:
CURRENT: 3.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES
 - ENVIRONMENTAL:
OPERATING TEMPERATURE RANGE -30° C ~ +80° C
 - Salt Spray:24H



BOM		
序号	名称	材料规格
1	Terminal	C2680 T=0.15mm 电镀金1u" Ni:50u"
2	卡勾	SUS301 3/4H T=0.15mm 素材
3	Molding 3	LCP 黑色 UL94 V-0
4	Shell	SUS201 1/4H T=0.30mm Ni:50u"



REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




24.00±0.3



ADHESIVE TAPE


PULL OUT DIRECTION



φ330

30.0

1000PCS/每卷



10卷/每箱

X. ±0.50	X° ± 2°	UNITS mm	深圳市创粤科技有限公司	
.X ±0.30	.X° ± 1°		TITLE:	
.XX ±0.10	.XX° ± 0.5°	MAT'L	TYPE-C 16PIN沉板0.8MM母座 长L=6.50MM	
.XXX ± 0.05			TYPE-C-16P-R0.8L6.5-34002	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD.		FINISH	CHKD:	DWG NO.:
			DR:	
		Q'TY		
			SCALE	SHEET
			1/1	1/1
				REV.
				A1