





技术指标 (Technical Index):

- 1. 工作温度 (Temperature range): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- 2. 额定电压 (Rated voltage): 250V DC/AC(rms) .
- 3. 额定电流 (Rated current): 9.5A (AWG#16~#18) AC, DC.
- 4. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
- 5. 耐压值 (Dielectric withstanding voltage): 1500V AC/minute .
- 6. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7. 适用线规 (Apply to gauge): T1: AWG#16~#18.
T2: AWG#20~#24.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		WF-MX3.0-DS2	MX3.0公头端子(大电流)		
X.XX±0.10		DESIGN: James	CUSTOMER 	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1