
Kinghelm®

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| REV | NUMBER | DESCRIPTION | DWN | CHK | DATE |
| A | | DESIGN | | | |
| | | | | | |




| ITEM NO. | PART NUMBER | DESCRIPTION | QTY. |
|---|---|---|---|
| ④ | 套管 | 黑色热缩套管，OD:2.0MM | AS |
| ③ | 端子 | 国产I-PEX1.13 1代端子，镀金 | 1 |
| ② | 接头 | SMA母头公针(反极性),11牙镀金,配件:华司/螺母/弹垫/红帽子 | 1 |
| ① | 同轴线 | RF1.13黑色同轴线,外被:FEP,OD:1.10mm | AS |

NOTES:

1. ELECTRICAL:
   - 1.1. VOLTAGE RATING:DCV 300V 10MS
   - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
   - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
   - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
   - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
   - 2.1. SEE TABLE
3. MECHANICALL:
   - 3.1. SMA PULL FORCE: 12.0KGS.
4. ALL COMPONENTS ARE RoHS COMPLIANT.

CUSTOMER P/N:

# 深圳市金航标电子有限公司

| | | | |
|---|---|---|---|
| ALL DIMENSION ARE IN MM | DRAWN Jamy | DATE 2026 /07 /10 | |
| | ENG. | | TITLE: KH-RPSMAK-IPEX-RG1.13-B250MM |
| COMPUTER GENERATED IN SOLIDWORKS | MFG. | | |
| DO NOT SCALE THIS DRAWING | Q.A. | | SIZE B / Number / REV A |
| PROJECTION | GENERAL TOLERANCE FOR ANGLES ± 1° X.X ± 0.3 X.XX ± 0.25 X.XXX ± 0.150 | | SCALE: Free / TYPE / SHEET 1 OF 1 |