





Recommended of Base hole





Washer


Schematic	Pin	PART.No
	2.0mm	DC-025MHA-A
	2.5mm	DC-025MHA-B

SPECIFICATION


1. Rating : DC 20V, 10A ;
2. Contact resistance: ≤0.03Ω;
3. Insulation resistance: ≥100MΩ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles。

LEAD FREE

NO.	DESCRIPTION	QTY	MATERIAL	REMARK
8	COVER NUT	1	H59	MB:Cu Ni PLATED
7	Washer	1	SPCC	Ni PLATED
6	HOUSING	1	PBT 4815	UL-94V0(BLACK)
5	AXIS SUPPORT	1	H59	MB:Cu Ni PLATED
4	PIN	1	H65	MB:Cu Ni PLATED
3	SPRING	1	C5191	MB:Cu Ag PLATED
2	CURVE PIECE	1	H65	MB:Cu Ag PLATED
1	FLAT PIECE	1	H65	MB:Cu Ag PLATED



Nut



T:1.6 Dimensions of PC board holes

Tolerance : ±0.1(Printed-top view)

QC:Inspection Item	DIMENSION IN mm [Inch]		浙江创都电子科技有限公司	
	TOLERANCE UNLESS OTHERWISE SPECIFIED		DWG NO	CAX-DC-025MHB-2.5X-5.7XL
	±0.5	°± °		
	±0.3	X.X °± 2°	TITLE DC JACK	CUSTORMER CO
	±0.25			
	APPROVE JACK	CHECK	DRAW	PROJ. SHEET 1 / 1
				SCALE 1:1 REV A1