



RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		











RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm




	1	2	3	4
DIM A	8.8	9.3	10.0	10.5
DIM B	0.8	1.0		



NOTES:

SPECIFICATION:

1. VOLTAGE: 100 VAC
2. TEMPERATURE RANGE: −30 °C ~ 85 °C
3. CONTACT RESISTANCE: 40 MILLIONHM MAX
4. INSULATION RESISTANCE: 100 MEGOHMS MIN.
5. LNSERTION FORCE : 5N~20N
6. UNMATING FORCE: 8N~20N
7. DURABILITY: 10,000 CYCLES



A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
5	SHELL	STAINLESS STEEL	NI Plated	1PCS
4	SPRING	STAINLESS STEEL	---	1PCS
3	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
2	CONTACT	COPPER ALLOY	Au1u"/NI Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS


X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 24P夹板0.8MM母座 L=10.5MM
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-24P-C0.8L10.5-08628
		Q'TY	CHKD:
			DR:

DWG NO.:


SCALE	SHEET	REV.
1/1	1/1	A1

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




① PVC真空管(50PCS/管)



② 50PCS/管,一捆20管/1000pcs



③ 50PCS/管,1捆20管,1箱10捆/10000pcs



④ 外箱封箱示意图

ITEM	DESC.	MATERIAL	REMARKS	QTY
1	成品		C TYPE母座成品	10000
2	真空管	pvc	L=14.5mm W=5.5mm H=470mm	200
3	小标签		L50mm*W70mm	10
4	外标签		L50mm*W70mm	1
5	外箱	A=A	L140mm*W490mm*H170mm	1

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 24P夹板0.8MM母座 L=10.5MM
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-24P-C0.8L10.5-08628 / DWG NO.:
		Q'TY	CHKD:
			DR:

SCALE	SHEET	REV.
1/1	1/1	A1